



5721 03UP61

5721 30UP61



Montageplatten **S. 84**, Rahmenplatten **S. 86**

IP 20

Abdeckrahmen Gr. I-I, 92 × 157 mm, Frontplatte 45 × 45 mm,
Befestigungsplatte Metall, 85 × 139 mm
Waagrechte und senkrechte Montage möglich

VE

UP-Kombination Gr. I-I, 10 A, 250 V

1		Leerplatz und Wechselschalter	leer - 3 / 1L	5721 01UP61 551 113 001	5721 01UP67 551 113 931	5721 01UP68 551 113 141
1		Doppel-Wechselschalter	3 / 1L - 3 / 1L	5721 03UP61 482 110 001	5721 03UP67 482 110 931	5721 03UP68 482 110 141
1		Doppel-Wechselschalter und Wechselschalter	3+3 / 1L - 3 / 1L	5721 04UP61 482 111 001	5721 04UP67 482 111 931	5721 04UP68 482 111 141
1		Wechselschalter und Wipptaster	3 / 1L - AR / 1L	5721 05UP61 482 142 001	5721 05UP67 482 142 931	5721 05UP68 482 142 141
1		Doppel-Wipptaster	AR / 1L - AR / 1L	5721 06UP61 482 150 001	5721 06UP67 482 150 931	5721 06UP68 482 150 141
1		Leerplatz und Sonnerietaster	leer - AR / 1L	5721 29UP61 482 146 001	5721 29UP67 482 146 931	5721 29UP68 482 146 141
1		Wechselschalter und Sonnerietaster	3 / 1L - AR / 1L	5721 30UP61 482 152 001	5721 30UP67 482 152 931	5721 30UP68 482 152 141
1		Wechselschalter beleuchtbar* und Sonnerietaster	(LS) 3 / 1L - AR / 1L	5721 32UP61 482 162 001	5721 32UP67 482 162 931	5721 32UP68 482 162 141
1		Blindabdeckung		5721 07UP61 378 510 001	5721 07UP67 378 510 931	5721 07UP68 378 510 141



UP

Gr. I-I



Weiss



UP

Gr. I-I



Pearl Alu



UP

Gr. I-I



Graphite