



# MyHOME® Hausautomation - BUS



## Automation - Bewegungsmelder

### ■ Erfassungsbereich

Art. HD/HC/HS4658 - 5740 48/98




Art. BMSE2006



		Empfindlichkeit (25%)			Empfindlichkeit (50%)		
		A	B	Oberfläche (m <sup>2</sup> )	A	B	Oberfläche (m <sup>2</sup> )
Höhe (m)	2,5	8	3	66	15	5	131
	3	8	3	66	15	5	131
	4	8	2	58	15	5	116
	5	8	2	53	15	4	105
	6	8	2	47	15	4	94

		Empfindlichkeit (75%)			Empfindlichkeit (100%)		
		A	B	Oberfläche (m <sup>2</sup> )	A	B	Oberfläche (m <sup>2</sup> )
Höhe (m)	2,5	23	8	197	30	10	263
	3	23	8	197	30	10	263
	4	23	7	174	30	9	233
	5	23	6	158	30	8	210
	6	23	5	141	30	7	188


Art. BMSE3001



		Empfindlichkeit							
A (m)	Niedrig		Mittelwert		Hoch		Maximum		
	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )	
2,5	4	15	6	25	6,5	30	8	50	
3	5,5	25	6,5	35	8,5	60	11,5	100	
4	6,5	35	7,5	45	12,5	125	14	155	
5	6	30	10,5	90	12	115	16,5	215	
6	4	15	5,5	25	8,5	60	12,5	125	

Legende:  
A = Höhe (Installation) (m)  
Ø = Durchmesser (m)  
S = Oberfläche (m<sup>2</sup>)

Art. BMSE3003



		Empfindlichkeit							
A (m)	Niedrig		Mittelwert		Hoch		Maximum		
	Tech.	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )	Ø (m)	S (m <sup>2</sup> )
2,5	PIR	4	15	6	25	6,5	30	8	50
	US	4	15	4	15	6	30	11	95
3	PIR	5,5	25	6,5	35	8,5	60	11,5	100
	US	6	30	6	60	8	50	13	150
4	PIR	6,5	35	7,5	45	12,5	125	14	155
	US	6	30	6	30	10	80	13	150
5	PIR	6	30	10,5	90	12	115	16,5	215
	US	6	30	6	30	10	80	13	130
6	PIR	4	15	5,5	25	8,5	60	12,5	125
	US	-	-	6	30	10	80	13	130

Legende:  
A = Höhe (Installation) (m)  
Ø = Durchmesser (m)  
S = Oberfläche (m<sup>2</sup>)